

# hi-tray metal

Special BSA stainless steel trays with 16.70% chrome



Lower Perforated



Lower Solid



Upper Perforated



Upper Solid

### USE

- Impression tray for standard applications

### CHARACTERISTICS

- Can be sterilized in a cold solution or in autoclave
- Available in two versions: solid and perforated

### ADVANTAGES

- High deformation strength
- Greater precision of the impression
- Designed for perfect mechanical retention of the material to the impression tray
- Soldering point accuracy
- Durability

### Packaging

#### Single Packs: Solid

SIZE	1	2	3	4	5
UPPER	D51SS	D52SS	D53SS	D54SS	D55SS
LOWER	D51IS	D52IS	D53IS	D54IS	D55IS

#### Single Packs: Perforated

SIZE	1	2	3	4	5
UPPER	D51SP	D52SP	D53SP	D54SP	D55SP
LOWER	D51IP	D52IP	D53IP	D54IP	D55IP

#### Kit Packs: 1 kit, 10 upper and lower trays each

D5K10S	Solid
D5K10P	Perforated

#### Kit Packs: 1 kit, 8 upper and lower trays each

D5K08S	Solid
D5K08P	Perforated